


# PCB Relay G5SB

Compact Single-pole Relay for Switching 5 A (Normally Open Contact), Fan Control of Air Conditioners, and Heating Control of Small Appliances.

- Environment-friendly, Pb-free.
- Compact SPDT Relay with high insulation.
- Incorporates a normally open contact that switches 5 A max.
- Ensures a withstand impulse voltage of 8,000 V between the coil and contacts.
- . Conforms to UL and CSA.
  - UL508
  - CSA C22.2 (No.14)
  - VDE approval is in progress.

**Note:** The G5S-1 will be discontinued at the end of March 2004. Please change to the G5SB (Environment-friendly Relay).



## **Ordering Information**

| Classification | Contact form | Protective structure | Model   |
|----------------|--------------|----------------------|---------|
| Standard       | SPDT         | Fully sealed         | G5SB-14 |

Note: When ordering, add the rated coil voltage to the model number.

Example: G5SB-14 12 VDC

Rated coil voltage

### **■** Model Number Legend

G5SB-QQQ VDC

- 1. Number of Poles
  - 1: SPDT
- 2. Protective Structure
  - 4: Fully sealed
- 3. Rated Coil Voltage

5, 9, 12, 24 VDC

## **Specifications**

## ■ Coil Ratings

| Rated voltage        | 5 VDC                    | 9 VDC                     | 12 VDC  | 24 VDC  |  |  |
|----------------------|--------------------------|---------------------------|---------|---------|--|--|
| Rated current        | 80 mA                    | 44.4 mA                   | 33.3 mA | 16.7 mA |  |  |
| Coil resistance      | 63 Ω                     | 202 Ω                     | 360 Ω   | 1,440 Ω |  |  |
| Must operate voltage | 75% max. of rated volta  | 75% max. of rated voltage |         |         |  |  |
| Must release voltage | 5% min. of rated voltage |                           |         |         |  |  |
| Maximum voltage      | 110% of rated voltage    |                           |         |         |  |  |
| Power consumption    | Approx. 400 mW           |                           |         |         |  |  |

#### **■** Contact Ratings

| Load                    | Resistive load  |
|-------------------------|---|
| Rated load              | 3 A (NO)/3 A (NC) at 125 VAC<br>5 A (NO)/3 A (NC) at 125 VAC<br>5 A (NO) at 250 VAC<br>3 A (NC) at 250 VAC<br>5 A (NO)/3 A (NC) at 30 VDC |
| Contact material        | Ag alloy  |
| Rated carry current     | 5 A (NO)/3 A (NC)   |
| Max. switching voltage  | 250 VAC, 30 VDC   |
| Max. switching current  | 5 A (NO)/3 A (NC)   |
| Max. switching capacity | 1,250 VA, 150 W (NO)<br>750 VA, 30 W (NC)   |
| Min. permissible load   | 10 mA at 5 VDC  |

**Note:** P level:  $\lambda 60=0.1 \times 10^{-6}$  operation (with an operating frequency of 120 operations/min.)

#### **■** Characteristics

| Contact resistance (See note 2.)    | 100 m $\Omega$ max.   |  |  |  |
|-------------------------------------|---|--|--|--|
| Operate time (See note 3.)          | 10 ms max.  |  |  |  |
| Release time (See note 3.)          | 5 ms max.   |  |  |  |
| Insulation resistance (See note 4.) | 1,000 M $\Omega$ min.   |  |  |  |
| Dielectric strength                 | 4,000 VAC, 50/60 Hz for 1 min between coil and contacts<br>1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity  |  |  |  |
| Impulse withstand voltage           | 8 kV (1.2 x 50 μs)  |  |  |  |
| Vibration resistance                | Destruction: 10 to 55 Hz, 0.75-mm single amplitude (1.5-mm double amplitude) Malfunction: 10 to 55 Hz, 0.75-mm single amplitude (1.5-mm double amplitude)   |  |  |  |
| Shock resistance                    | Destruction: 1,000 m/s² (approx. 100G) Malfunction: Energized: 100 m/s² (approximately 10G) Non-energized: 100 m/s² (approximately 10G)   |  |  |  |
| Durability (See note 5.)            | Mechanical: 5,000,000 operations (18,000 operations per hour)  Electrical: 200,000 operations: 3 A (NO)/3 A (NC) at 125 VAC resistive load 50,000 operations: 5 A (NO)/3 A (NC) at 125 VAC resistive load 50,000 operations: 5 A (NO) at 250 VAC resistive load 10,000 operations: 3 A (NC) at 250 VAC resistive load 10,000 operations: 5 A (NO)/3 A (NC) at 30 VDC resistive load  Switching frequency: 1,800 operations per hour |  |  |  |
| Ambient temperature                 | Operating: -40°C to 70°C with no icing or condensation  |  |  |  |
| Ambient humidity                    | Operating: 5% to 95%  |  |  |  |
| Weight                              | Approx. 6.5 g   |  |  |  |

- Note: 1. The data shown above are initial values.
  - 2. The contact resistance is possible with 1 A applied at 5 VDC using a fall-of-potential method.
  - 3. The operating time is possible with the operating voltage imposed with no contact bounce at an ambient temperature of 23°C.
  - 4. The insulation resistance is possible between coil and contacts and between contacts of the same polarity at 500 VDC.
  - **5.** The electrical durability data items shown are possible at 23°C.

#### ■ Approved Standards

### **UL508 (File No. E41515)**


## CSA C22.2 (No. 14) (File No. LR31928)

| Model | Coil ratings | Contact ratings   | Number of test operations |
|-------|--------------|---|---------------------------|
| G5SB  |              | 3 A, 125 VAC (resistive) NC only<br>2 A, 125 VAC (resistive) NC only<br>5 A, 250 VAC (resistive) NO only<br>3 A, 250 VAC (resistive) NO only<br>5 A, 30 VDC (resistive) NO only | 6,000                     |


Electrical durability tests are performed at 70°C.

# **Engineering Data**

#### Max. Switching Capacity




#### **Ambient Temperature vs. Maximum Voltage**




## **Dimensions**

Note: All units are in millimeters unless otherwise indicated.



# PCB Mounting Holes (Bottom View)



Terminal Arrangement/ Internal Connections (Bottom View)



Note: Values in parentheses are average values

# **Application Examples**

- **■** Fan Motor
- Oven
- Refrigerator
- **■** Washing Machine
- **■** Air Conditioner
- Others

#### ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. K122-E1-01 In the interest of product improvement, specifications are subject to change without notice.

### **OMRON Corporation**

Electronic Components Company

**C&C Components Division H.Q.** Shiokoji Horikawa, Shimogyo-ku Kyoto, 600-8530 Japan

Tel: (81)75-344-7097/Fax: (81)75-344-7049

Printed in Japan 0702-1M (0702) (S)